

Sample Software

Sample Software

Application System

Machine Vision

Manual Positions

Motion Control Products

Optical & Mirror Holder

Optomechanics

Holders

Factory Automation Parts

Measurement & Control

FA Electrical Parts

Laser

Tools & Clean Parts

Nanometer Stages

Precision Linear Motorized Stages

High Speed Motorized Stages

Motorized Goniometer

Multiaxis Motorized Stages

Motorized Rotation Stages

Industrial Robot

Controller & Driver & Cable

Custom-Built Motorized Stages

Software	Download
<p>SG Sample (Ver.1.1.8) for 32/64 bit Windows(RS232C) (for SHOT-102/302GS/304GS/702, GSC-01/02, FINE-01Gamma/503, PKA-ID-02, OMEC-2BG/4BG, GIP-101,GIP-101B,PGC-04/-U,HIT-M,HSC-103,ECC100,RMC-102)</p> <ul style="list-style-type: none"> ● Control the Stage ● Terminal Window(ECC100 except.) ● Update the MemorySwitch(SHOT-102,GSC,OMEC,GIP,ECC100,RMC-102 except.) ● Update the Program(SHOT-102/702,GSC,PKA,OMEC,GIP,ECC100,RMC-102 except.) ● Simple Excel Instruction(PGC-04/-U,HIT-M,HSC-103,ECC100 except.) 	<p>DOWNLOAD :23.9MB</p>
<p>SG Commander (Ver.12.6.0) for 32/64 bit (RS232C) (for SHOT(Mark)-102/202/204, FINE(Mark)-501/502/503, FINE-01,SHOT-302GS/304GS, PAT-001,OMEC-2BF/2BG/4BF/4BG, SHOT-602, CSG-602R/522R, MINI-5D, BS-302GS/304GS, PKA-ID-02, SHOT-702,GSC-01/02, FINE-01 Gamma,GIP-101)</p> <ul style="list-style-type: none"> ● Control the Stage ● Terminal Window ● Update the MemorySwitch(SHOT-102/602,CSG,GSC,OMEC,GIP except.) ● Update the Program(SHOT-102/602/702,CSG,GSC,PKA,OMEC,GIP except.) ● Simple Excel Instruction(SHOT-102/602,CSG,GSC-02,MINI,BS except.) 	<p>DOWNLOAD :4.0MB</p>
<p>LabVIEW_Sample for RS232C/GPIB/(TCP/IP) (for version 2014/2015/2016/2017/2018) (for SHOT-202/204/302/304, GSC-01/02,HIT-M,PGC-04(U),HSC-103)</p>	<p>DOWNLOAD :2.4MB</p>
<p>LabVIEW for RS232C (for version 5.1) (for SHOT(Mark)-102/202/204/302/304, SHOT-602, CSG-602R/522R/532R, MINI-5D, PAT-001, FINE)</p>	<p>DOWNLOAD :1.3MB</p>
<p>LabVIEW for GPIB (for version 5.1) (for SHOT(Mark)-102/202/204/302/304,MINI-5D)</p>	<p>DOWNLOAD :0.9MB</p>
<p>LabVIEW for RS232C (for version 6i) (for SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, HIT)</p>	<p>DOWNLOAD :1.0MB</p>
<p>LabVIEW for GPIB (for version 6i) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)</p>	<p>DOWNLOAD :0.4MB</p>
<p>LabVIEW for RS232C (for version 7.1) (for SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, HIT,GIP-101)</p>	<p>DOWNLOAD :1.1MB</p>
<p>LabVIEW for GPIB (for version 7.1) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)</p>	<p>DOWNLOAD :0.5MB</p>

Sample Software

Software	Download
LabVIEW for RS232C (for version 8.6) (for SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, HIT,GIP-101)	DOWNLOAD :0.8MB
LabVIEW for GPIB (for version 8.6) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for RS232C (for version 2010) (for SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, HIT,GIP-101)	DOWNLOAD :0.9MB
LabVIEW for GPIB (for version 2010) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for RS232C (for version 2012) (for SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, HIT,GIP-101)	DOWNLOAD :0.9MB
LabVIEW for GPIB (for version 2012) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for RS232C (for version 2013) (for SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, HIT,GIP-101)	DOWNLOAD :0.9MB
LabVIEW for GPIB (for version 2013) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for RS232C (for version 2014) (for HIT-M,PGC-04,SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, HIT,GIP-101)	DOWNLOAD :1.1MB
LabVIEW for GPIB (for version 2014) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for RS232C (for version 2015) (for HIT-M,PGC-04,HSC-103,SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, OMEC,GIP-101)	DOWNLOAD :1.3MB
LabVIEW for GPIB (for version 2015) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for RS232C (for version 2016) (for HIT-M,PGC-04,HSC-103,SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, OMEC,GIP-101)	DOWNLOAD :1.3MB
LabVIEW for GPIB (for version 2016) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB

Application System

Machine Vision

Manual Positions

Motion Control Products

Optical & Mirror Holder

Optomechanics

Holders

Factory Automation Parts

Measurement & Control

FA Electrical Parts

Laser

Tools & Clean Parts

Nanometer Stages

Precision Linear Motorized Stages

High Speed Motorized Stages

Motorized Goniometer

Multiaxis Motorized Stages

Motorized Rotation Stages

Industrial Robot

Controller & Driver & Cable

Custom-Built Motorized Stages

Sample Software

Application System

Machine Vision

Manual Positions

Motion Control Products

Optical & Mirror Holder

Optomechanics

Holders

Factory Automation Parts

Measurement & Control

FA Electrical Parts

Laser

Tools & Clean Parts

Nanometer Stages

Precision Linear Motorized Stages

High Speed Motorized Stages

Motorized Goniometer

Multiaxis Motorized Stages

Motorized Rotation Stages

Industrial Robot

Controller & Driver & Cable

Custom-Built Motorized Stages

Software	Download
LabVIEW for RS232C (for version 2017) (for HIT-M,PGC-04(U),HSC-103,SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, OMEC,GIP-101)	DOWNLOAD :1.4MB
LabVIEW for GPIB (for version 2017) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for TCP/IP (for version 2017) (for HIT-M,PGC-04(U))	DOWNLOAD :0.3MB
LabVIEW for RS232C (for version 2018) (for HIT-M,PGC-04(U),HSC-103,SHOT(Mark)-102/202/204/302/304, SHOT-602/GSC-02, CSG-602R/522R/532R, PAT-001/GSC-01, FINE(Mark)-01(r)/503, SHOT-702, OMEC,GIP-101)	DOWNLOAD :1.4MB
LabVIEW for GPIB (for version 2018) (for SHOT(Mark)-102/202/204/302/304,FINE(Mark)-503)	DOWNLOAD :0.4MB
LabVIEW for TCP/IP (for version 2018) (for HIT-M,PGC-04(U))	DOWNLOAD :0.3MB
BIOSControl(Ver.1.0.2) (for SHOT-702/302GS,FC-101G/401G,501G,SC-101G)	DOWNLOAD :1.5MB
SSH-C4B_sample(Ver.1.0.2) (for SSH-C4B)	DOWNLOAD :749KB
SSH-C2B_Demo_Software (for SSH-C2B)	DOWNLOAD :1.5MB
OSCAMS (for SPVNIR-05-CS) Windows7(32/64bit version) Windows8.1(64bit version) Windows10(64bit version)	DOWNLOAD :170MB