

α Axis Goniometers

α Axis Goniometers / $\alpha\beta$ Axis Goniometers

GOH-15A

Stage Size 15 × 15 mm

RoHS

GOH-25A/25B

Stage Size 25 × 25 mm

RoHS

Goniometers with dovetail slide and worm gear construction for angular adjustment of heavy loads.

- GOH-15A model : Smallest Goniometer available, exclusively from OptoSigma.
- GOH-25A model : Vernier scales for reading angular position. Locking mechanism clamps dovetail to minimize movement.



Guide

- To operate the GOH-15A10, a 2.5mm hex wrench is required and is included with stage.

Attention

- Due to size limitations, the GOH-15A10 does not include a scale or clamping mechanism.
- Locking mechanism is operated using thumbscrew on side of stage.

Specifications								
Part Number	METRIC	GOH-15A10	GOH-25A18	GOH-25A30	GOH-25A40	GOH-25B18	GOH-25B30	
(Opposite Model)	METRIC	—	GOH-25A18R	GOH-25A30R	GOH-25A40R	GOH-25B18R	GOH-25B30R	
Stage Size [mm]		15×15	25×25	25×25	25×25	25×25	25×25	
Axes of Travel		α axis				$\alpha\beta$ axis		
Rotation Center Height [mm]		10±0.1	18±0.1	30±0.1	40±0.1	18±0.1	30±0.1	
Angle Range [°]	(Upper) β axis	—	—	—	—	±20	±15	
	(Lower) α axis	±20	±20	±15	±10	±15	±10	
Vernier Readable Resolution		—	12′	12′	12′	12′	12′	
Travel per Knob Rotation [°]	(Upper) β axis	—	—	—	—	about 3.1	about 2.17	
	(Lower) α axis	about 5	about 3.1	about 2.17	about 1.67	about 2.17	about 1.67	
Rotation Center Displacement [mm]		φ0.1 or less	φ0.1 or less	φ0.1 or less	φ0.1 or less	φ0.1 or less	φ0.1 or less	
Guide Method		Dovetail slide method						
Primary Material		Brass						
Finish		Super black chrome						
Load Capacity [N]		9.8 (1.0kgf)	19.6 (2.0kgf)	19.6 (2.0kgf)	19.6 (2.0kgf)	19.6 (2.0kgf)	19.6 (2.0kgf)	
Max. Moment Capacity	Pitch [N·m]	0.03	0.35	0.35	0.35	0.35	0.35	
	Roll [N·m]	0.05	0.4	0.4	0.4	0.35	0.35	
Moment Stiffness	Roll [°/N·cm]	—	1.0	1.0	1.0	—	—	
Parallelism [μm]		50	50	50	50	100	100	
Weight [kg]		0.02	0.07	0.06	0.06	0.13	0.12	

Application Systems

Optics & Optical Coatings

Opto-Mechanics

Bases

Manual Stages

Actuators & Adjusters

Motorized Stages

Light Sources & Laser Safety

Index

Guide

X Axis Stages

XY Axis Stages

Z Axis Stages

XZ Axis Stages

XYZ Axis Stages

Rotation Stages

Goniometer

Tilt Stages

Vacuum

Ball Bearing Guide

Crossed Roller

Dovetail

Lapping

V Groove Screw

Others

15 × 15 mm

25 × 25 mm

40 × 40 mm

60 × 60 mm

65 × 65 mm

80 × 80 mm

100 × 100 mm


120 × 120 mm

Others




Outline Drawing

GOH-15A10 Pan head screw M2×5...2 screws 2.5mm




GOH-25A** Pan head screw M2×4...4 screws 2.5mm




Part Number	A (mm)	B (mm)
GOH-25A18	12	18
GOH-25A30	10	30
GOH-25A40	10	40

GOH-25AR** Pan head screw M2×4...4 screws 2.5mm




Part Number	A (mm)	B (mm)
GOH-25A18R	12	18
GOH-25A30R	10	30
GOH-25A40R	10	40

GOH-25B** Pan head screw M2×4...4 screws



Part Number	A (mm)	B (mm)	C (mm)
GOH-25B18	12	22	18
GOH-25B30	10	20	30

GOH-25BR** Pan head screw M2×4...4 screws



Part Number	A (mm)	B (mm)	C (mm)
GOH-25B18R	12	22	18
GOH-25B30R	10	20	30

Application Systems

Optics & Optical Coatings

Opto-Mechanics

Bases

Manual Stages

Actuators & Adjusters

Motorized Stages

Light Sources & Laser Safety

Index

Guide

X Axis Stages

XY Axis Stages

Z Axis Stages

XZ Axis Stages

XYZ Axis Stages

Rotation Stages

Goniometer

Tilt Stages

Vacuum

Ball Bearing Guide

Crossed Roller

Dovetail

Lapping

V Groove Screw

Others

15 × 15 mm

25 × 25 mm

40 × 40 mm

60 × 60 mm

65 × 65 mm

80 × 80 mm

100 × 100 mm

120 × 120 mm

Others