

Rubber tile vibration isolators are designed to be placed at the four corners of an optical laboratory bench or other equipment to reduce vibrations.



**Attention**

► Recommended maximum load is 4.9N/cm<sup>2</sup> (about 5kgf/cm<sup>2</sup>)

**Specifications**

Part Number	External Dimensions [mm]	Thickness [mm]	Weight per Sheet [kg]	Quantity [Pieces]
PR-1010	100×100	10	0.12	4
PR-1515	150×150	10	0.27	4
PR-3030	300×300	10	1.1	1

Application Systems

Optics & Optical Coatings

Opto-Mechanics

**Bases**

Manual Stages

Actuators & Adjusters

MotORIZED Stages

Light Sources & Laser Safety

Index

**Guide**

Vibration Isolation Systems

**Optical Tables**

Darkrooms/ Dark Boxes

Optical Bases

Posts

Brackets

Adapters

Tools