VBSP

NEW RoHS



Low out-gas base plates for fixing vacuum holders and vacuum stages in the optical baseplates.

- •Long cut out hole enables the smooth base plate positioning and helps fixing in the optimal position.
- •Screw hole grooving and vent hole processing are applied to prevent the out-gas emits when forming vacuum.
- •Besides the post holders, 25mm and 40mm stainless stages (TSDS-251, TSDS-401) can be fixed.

Guide

- We deliver the item with specialized vacuum packaging to keep its high clean state from the factory to the destination.
- ► We provide vacuum optical baseplates (VOBC) for fixing the post holders.

Attention


- ▶ Screws are not included. Please prepare vacuum screws (VPCB/VAGB).
- ▶ Please open the package in the clean environment. Please do not touch it by your bare hands.

Outline Drawing				
VBSP-2460	SUS Stainless steel washers2 screw			
	60 35 20 4-M2 depth 5 M16 P1	10		
VBSP-40100	Both sides outlet slots			
	SUS Stainless steel washers2 screw			
_	100			

Specifications	Primary material: Steel(SUS316L) Finish : None	
Part Number	Weight [kg]	Compatible Mounting Screw Number
VBSP-2460	0.078	VPCB-6-20
VBSP-40100	0.260	or VAGB-6-20



Οι



RoHS

NEW

VBSC



Low out-gas base clamps for fixing vacuum optical baseplates and vacuum base plate to the tables in the high vacuum chamber.

- •Long hole and vacuum M6 screw enables fixing the 10mm thickness plates in the optimal position.
- •If screws are tightened, plates are pressed firmly to the tables by leverage and the plates will be fixed.

Attention

- ▶ Screws are not included. Please prepare vacuum screws (VPCB/VAGB).
- ▶ Please open the package in the clean environment. Please do not touch it by your bare hands.

Specifications	Primary material: Aluminum(A6061) Finish: None		
Part Number	Weight [kg]	Compatible Mounting Screw Number	
VBSC-60	0.03	VPCB-6-20 or VAGB-6-20	



VBSC-60

SUS Stainless steel washers...1screw

8

